



Your Laundry & Infection Control Partner

# JLA 16, 22, 30 and 35

Free-standing, High Speed Spin Washers



JLA 16

JLA 22

JLA 30

JLA 35

THE PROFESSIONALS CHOICE

## SPECIFICATIONS

Details	Units	JLA 16	JLA 22	JLA 30	JLA 35
Capacity	Kg(lb)	7.6(16)	9.5(22)	13.2(30)	16.5(35)
Height	mm	1038	1038	1202	1202
Width	mm	660	660	780	780
Depth	mm	796	896	904	1004
Net Weight	Kg	211	236	325	358
Drum Volume	m <sup>3</sup> /l	0.072/72	0.095/95	0.131/131	0.164/164
G Force - Low/High spin	Gs	74/296	74/296	88/363	88/363
Door Opening	Ø mm	300	300	300	300
Electrics - 9KW Heater (1ph)	Volt/ph/Amp	240/1/45(s)	240/1/45	240/1/45	240/1/45
Electrics - 6KW Heater	Volt/ph/Amp	240/1/32	240/1/32	240/1/32	240/1/32
Electrics - Steam Heated	Volt/ph/Amp	240/1/10	240/1/10	240/1/16	240/1/16
Electrics - 12KW Heater	Volt/ph/Amp	n/a	415/3/32(s)	415/3/32(s)	415/3/32(s)
Electrics - 9KW Heater (3ph)	Volt/ph/Amp	415/3/20	415/3/20	-	-
No. of Water Connections	Cold/Hot	2/1	2/1	2/1	2/1
Connection Size	"BSP	3/4	3/4	3/4	3/4
Drain Connection (Gravity)*	Ø mm	50	50	50	50
Steam Rating	Kg(lb)/cycle	7.5(16.5)	9.5(21)	3.2(29)	16.5(36)
Connection Size	"BSP	3/8	3/8	3/8	3/8

All specifications subject to change without notice

\*Machines are supplied as standard with 2 drain connections at 80mm and 155mm high. These are maximum heights with the levelling feet in place. In extreme cases optional raising legs can be supplied which will increase the height by a further 75mm or 125mm respectively.

# JLA 16, 22, 30 and 35

## Free-standing, High Speed Spin Washers

Machines in this range are ideal for contamination risk sites such as hospitals, care homes, hotels and veterinary surgeries. They meet NHS Guideline HSG (95)18, Category 5 of the latest Water Regulations and comply with the National Minimum Care Standards. Suitable for OTEX Validated Disinfection System.

### Features

Built-in Type 'A' air gap

Microprocessor controlled

Information display

Free-standing

Two spin speeds

Two sluice programmes

High build quality

Liquid soap injection control board

Choice of two drain heights

### Benefits

Eliminates the risk of water contamination and fully approved for direct connection to mains water, resulting in lower installation costs.

Standard with customised wash cycles to suit individual needs.

Displays cycle selected, operating temperature, minutes remaining until the end of cycle enabling more efficient use of staff time.

Lower installation cost. No bolting down required.

1,000rpm super spin, reduces drying time by up to 30% - saves cost, increases throughput and eliminates need for separate hydro extractor. Standard spin speed for delicates prevents creasing and fabric damage.

Separate programmes for both thermal and chemical disinfection depending on type of fabric being processed. Enables all laundry including heat labile fabrics to be processed without handling foul or infected items.

Stainless steel cabinet and drum - clean and hygienic, robust and reliable.

Easy connection to auto-dosing pump system.

Usually no need for a raising plinth.

## For further information call 0800 591903

**JLA Limited** Meadowcroft Lane, Ripponden, West Yorkshire HX6 4AJ

**T** 01422 822282 **F** 01422 824390 **email** info@jla.com

**JLA Limited** Regus House, Harcourt Road, Dublin 2 **T** 01 477 3915 **F** 01 402 9590