



## JLA16, 22, 30 and 35 Industrial Free-standing, High Speed Spin Washers

Machines in this range are ideal for contamination risk sites such as hospitals, care homes, hotels, prisons and veterinary surgeries. They meet NHS Guideline HSG (95)18, Category 5 of the latest Water Regulations and comply with the National Minimum Care Standards. Robustly built with a stainless steel finish, they feature a high-speed spin which dramatically reduces drying time and a standard spin for delicates. They are free-standing for lower installation costs and have microprocessor controls for easy operation. Suitable for OTEX Validated Disinfection System.



Your Laundry & Infection Control Partner

## SPECIFICATION

Details	Units	JLA 16	JLA 22	JLA 30	JLA 35
Capacity	Kg(lb)	7.6(16)	9.5(22)	13.2(30)	16.5(35)
Height	mm	1038	1038	1202	1202
Width	mm	660	660	780	780
Depth	mm	796	896	904	1004
Net Weight	Kg	211	236	325	358
Drum Volume	m <sup>3</sup> /l	0.072/72	0.095/95	0.131/131	0.164/164
G Force - Low/High spin	Gs	74/296	74/296	88/363	88/363
Door Opening	Ø mm	300	300	300	300
Electrics - 9KW/Heater (1ph)	Volt/ph/Amp	240/1/45(s)	240/1/45	240/1/45	240/1/45
Electrics - 6KW Heater	Volt/ph/Amp	240/1/32	240/1/32	240/1/32	240/1/32
Electrics - Steam Heated	Volt/ph/Amp	240/1/10	240/1/10	240/1/16	240/1/16
Electrics - 12KW Heater	Volt/ph/Amp	n/a	415/3/32(s)	415/3/32(s)	415/3/32(s)
Electrics - 9KW Heater (3ph)	Volt/ph/Amp	415/3/20	415/3/20	-	-
No. of Water Connections	Cold/Hot	2/1	2/1	2/1	2/1
Connection Size	"BSP	3/4	3/4	3/4	3/4
Drain Connection (Gravity)*	Ø mm	50	50	50	50
Steam Rating	Kg(lb)/cycle	7.5(16.5)	9.5(21)	13.2(29)	16.5(36)
Connection Size	"BSP	3/8	3/8	3/8	3/8

All specifications subject to change without notice

\*Machines are supplied as standard with 2 drain connections at 80mm and 155mm high. These are maximum heights with the levelling feet in place. In extreme cases optional raising legs can be supplied which will increase the height by a further 75mm or 125mm respectively.

**Built-in Type 'A' air gap complies with relevant Water Regulations.**

**Microprocessor controls for easy use.**

**Free-standing for lower installation costs.**

**1,000rpm super spin reduces drying time by up to 30%. Standard spin speed for delicates.**

**Two sluice programmes for both thermal and chemical disinfection.**

**High build quality with stainless steel finish.**

**Liquid feed detergent option.**

**Choice of two drain heights, no need for a raising plinth.**

**OTEX ready.**



**0800 591903**

[www.jla.com](http://www.jla.com)

**England and Wales** Meadowcroft Lane, Ripponden, West Yorkshire HX6 4AJ

**Scotland** Ardee, 27 Tollpark Place, Wardpark East, Cumbernauld, G68 0LN

**Ireland** Regus House, Harcourt Road, Dublin 2



Your Laundry & Infection Control Partner